



1 ×
BESC. 754

1 × BESC. 753

M: 1:1

0 10 20 30 40 50 60 70 mm

2 ×
BESC. 847

4 ×
BESC. 849
6 × 35 mm

2 ×
BESC. 772



4 ×
BESC. 770




8 ×
SCHR. 370
M5 × 25 mm

12 ×
SCHR. 371
6,3 × 12 mm


2 ×
SCHR. 342
3,5 × 15 mm

4 ×
SCHR. 396
5 × 40 mm






12



2x

 BESC. 847


13



4x

 BESC. 849
 6 x 35 mm


14



2x

 BESC. 772

15



1x

 BESC. 754

2x

 SCHR. 342
 3,5 x 15 mm

16



17



